



# Pacific II TCW097

## TCW097 2xTL-D36W HFS 220V 50Hz

2, MASTER TL-D, 36 W, Electronic standard, 220 to 230 V, 50 to 60 Hz

Functional impact-, dust- and jetproof luminaire for single and twin TLD and TL5 fluorescent lamps for indoor applications and semioutdoor applications. Housing and cover of TCW097 are made of high quality poly-carbonate which has an excellent impact resistant property. The cover has anti-UV additives which bring additional performance levels to UV protection. Available with conventional or high-frequency (HF) electronic control gears. Can be ceiling mounted or suspended. Equipped with mounting brackets, mounting is made easy via screws without drilling into the luminaire housing. Gear tray and metal toggles are re-installed; cable gland and mounting brackets are delivered with the luminaire.


### Product data

General Information	
Lamp family code	TL-D [MASTER TL-D]
Gear	EBS [Electronic standard]
Light Technical	
Number of light sources	2
Operating and Electrical	
Input Voltage	220 to 230 V
Line Frequency	50 to 60 Hz
Power Consumption	36 W
Approval and Application	
Protection class IEC	Safety class I

Product Data	
Order product name	TCW097 2xTL-D36W HFS 220V 50Hz
Full product name	TCW097 2xTL-D36W HFS 220V 50Hz
Full product code	911400866980
Order code	911400866980
Material Nr. (12NC)	911400866980
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4

# Pacific II TCW097

## Dimensional drawing



TCW097	118 114	136 128	158 135	218 214	236 228	258 235
LxWxH(mm)	660x100x110	1270x100x110	1570x100x110	660x150x110	1270x150x110	1570x150x110

