



TCH086

TCH086 TL5-28W/840 HF 220-240V

TL5, 28 W, 840 neutral white, Electronic high-frequency, 220 to 240 V

When it comes to selecting a batten, customers want a trunkable solution that combines safety and lifetime reliability with a slim design and ease of installation – so that they can meet the different requirements of different applications. Our T5 Essential Batten is extremely safe, highly reliable and offers significant energy savings compared with a T8 batten. With its slim housing it is easy to install and conceal in tight spaces, and trunking is straightforward.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HF [Electronic high-frequency]
Service tag	Yes
Light Technical	
Number of light sources	1
Light source color	840 neutral white
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	28 W
Approval and Application	
Ingress protection code	IP20 [Finger-protected]

Protection class IEC	Safety class II
Product Data	
Order product name	TCH086 TL5-28W/840 HF 220-240V
Full product name	TCH086 TL5-28W/840 HF 220-240V
Full product code	911400874080
Order code	911400874080
Material Nr. (12NC)	911400874080
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163288697
Numerator - Packs per outer box	24

TCH086

Dimensional drawing

