



TCH086

TCH084 TL5-28W/865 HF 220-240V

TL5, 28 W, 865 cool daylight, Electronic high-frequency, 220 to 240 V

When it comes to selecting a batten, customers want a trunkable solution that combines safety and lifetime reliability with a slim design and ease of installation – so that they can meet the different requirements of different applications. Our T5 Essential Batten is extremely safe, highly reliable and offers significant energy savings compared with a T8 batten. With its slim housing it is easy to install and conceal in tight spaces, and trunking is straightforward.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HF [Electronic high-frequency]
Service tag	Yes
Light Technical	
Light source color	865 cool daylight
Operating and Electrical	
Input Voltage	220 to 240 V
Power Consumption	28 W

Product Data	
Order product name	TCH084 TL5-28W/865 HF 220-240V
Full product name	TCH084 TL5-28W/865 HF 220-240V
Full product code	911400874380
Order code	911400874380
Material Nr. (12NC)	911400874380
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163288611
Numerator - Packs per outer box	24
EAN/UPC - Case	8710163288864

TCH086

Dimensional drawing

