



# Velocity

## SGP338 SON-T150W 230V-50Hz GB RAL7040

SON-T, 150 W, 230 V, 50 Hz, Glass bowl/cover

Road lighting luminaire for tubular high-pressure sodium lamps up to 400W. Step dimming option available up to SON-T 250W lamp version.

### Product data

General Information	
Lamp family code	SON-T [SON-T]
Gear	CONV [Conventional]
Light Technical	
Number of light sources	1
Optical cover type	Glass bowl/cover
Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Power Consumption	150 W
Approval and Application	
Ingress protection code	IP43/65 [Wire-protected, rain/spray-proof; dust penetration-protected, jet-proof]

Product Data	
Order product name	SGP338 SON-T150W 230V-50Hz GB RAL7040
Full product name	SGP338 SON-T150W 230V-50Hz GB RAL7040
Full product code	911400997880
Order code	911400997880
Material Nr. (12NC)	911400997880
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## Velocity

### Dimensional drawing

