



# Velocity

## SGP338 SON-T250W 220V-50Hz GB SD RAL7040

SON-T, 250 W, 220 V, 50 Hz, Glass bowl/cover

Road lighting luminaire for tubular high-pressure sodium lamps up to 400W. Step dimming option available up to SON-T 250W lamp version.

### Product data

General Information	
Lamp family code	SON-T [SON-T]
Cap-Base	- [-]
Gear	-
Light Technical	
Optical cover type	Glass bowl/cover
Operating and Electrical	
Input Voltage	220 V
Line Frequency	50 Hz
Power Consumption	250 W

Mechanical and Housing	
Housing Color	-
Product Data	
Order product name	SGP338 SON-T250W 220V-50Hz GB SD RAL7040
Full product name	SGP338 SON-T250W 220V-50Hz GB SD RAL7040
Full product code	911400998280
Order code	911400998280
Material Nr. (12NC)	911400998280
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## Velocity

### Dimensional drawing

