



Velocity

SGP338 SON-T250W 220V-50Hz GB SD RAL7040

SON-T - 250 W - 220 V - 50 Hz - Glass bowl/cover - Step dimming

Road lighting luminaire for tubular high-pressure sodium lamps up to 400W. Step dimming option available up to SON-T 250W lamp version.

Product data

General Information	
Lamp family code	SON-T [SON-T]
Lamp power	250 W
Cap base	- [-]
Compensation circuit	-
Gear	-
Optical cover/lens type	GB [Glass bowl/cover]
Light regulation	Step dimming
Country version	NO [Norway]
RAL colour	Window gray (7040)


Operating and Electrical	
Maximum lamp power	No [-]
Input voltage	220 V
Input frequency	50 Hz

Mechanical and Housing	
Colour	-

Product Data	
Full product code	911400998280
Order product name	SGP338 SON-T250W 220V-50Hz GB SD RAL7040
Order code	911400998280
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	911400998280
Net weight (piece)	12.850 kg

Velocity

Dimensional drawing



Velocity SGP338

