



Broadway SGP268

SGP268 SON-T250W 230V-50Hz GB RAL7040

SON-T, 250 W, 230 V, 50 Hz, Glass bowl/cover, Window gray (RAL7040)

A road lighting luminaire which embodies functionality and aesthetics, reflecting the aspirations of today modern cities. A step dimming option is available for SON-T 400W and SON 250W lamp versions.

Product data

| General Information | |
|--------------------------|---------------------|
| Lamp family code | SON-T [SON-T] |
| Gear | CONV [Conventional] |
| Light Technical | |
| Number of light sources | 1 |
| Optical cover type | Glass bowl/cover |
| Optic type outdoor | - |
| Operating and Electrical | |
| Input Voltage | 230 V |
| Line Frequency | 50 Hz |
| Power Consumption | 250 W |
| Mechanical and Housing | |
| Housing Color | - |

| Approval and Application | |
|---------------------------------|---|
| Ingress protection code | IP43/65 [Wire-protected, rain/spray-proof; dust penetration-protected, jet-proof] |
| Product Data | |
| Order product name | SGP268 SON-T250W 230V-50Hz GB RAL7040 |
| Full product name | SGP268 SON-T250W 230V-50Hz GB RAL7040 |
| Full product code | 911400998880 |
| Order code | 911400998880 |
| Material Nr. (12NC) | 911400998880 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |

Broadway SGP268

Dimensional drawing

