



Broadway SGP268

SGP268 SON-T400W 230V-50Hz GB RAL7040

SON-T, 400 W, 230 V, 50 Hz, Glass bowl/cover, Window gray (RAL7040)

A road lighting luminaire which embodies functionality and aesthetics, reflecting the aspirations of today modern cities. A step dimming option is available for SON-T 400W and SON 250W lamp versions.

Product data

General Information	
Lamp family code	SON-T [SON-T]
Gear	CONV [Conventional]
Light Technical	
Number of light sources	1
Optical cover type	Glass bowl/cover
Optic type outdoor	-
Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Power Consumption	400 W
Mechanical and Housing	
Housing Color	-

Approval and Application	
Ingress protection code	IP43/65 [Wire-protected, rain/spray-proof; dust penetration-protected, jet-proof]
Product Data	
Order product name	SGP268 SON-T400W 230V-50Hz GB RAL7040
Full product name	SGP268 SON-T400W 230V-50Hz GB RAL7040
Full product code	872016954581600
Order code	911400998980
Material Nr. (12NC)	911400998980
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169545816
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169545816

Broadway SGP268

Dimensional drawing

