



Savio TPS760 C

TPS762 C 2xTL5-28W HFP AC-MLO FU SMS

2, TL5, 28 W, HF Performer, Acrylate micro-lens optic

Featuring Philips' patented micro-lens optic technology, Savio is a complete luminaire range that offers the ideal combination of stylish design and optimum performance for both task and general lighting. Savio has an edge-to-edge lighting appearance with a uniform and comfortable brightness impression – a real 'surface of light'. The micro-lens optic consists of a single plate and is embedded in a housing made of high-quality natural anodized aluminum. Savio ensures optimum light distribution and full glare control in compliance with the latest office-lighting norm (EN 12464-1). Savio luminaires with Dynamic Lighting keep us feeling active by creating dynamic artificial light that varies over the course of the day or is set according to personal preference. Savio is available as suspended and surface-mounted.

Product data

General Information		Approval and Application	
Lamp family code	TL5 [TL5]	Ingress protection code	IP40 [Wire-protected]
Gear	HFP [HF Performer]	Mech. impact protection code	IK03 [0.3 J]
Flammability mark	For mounting on normally flammable surfaces	Protection class IEC	Safety class I
Light Technical		Product Data	
Number of light sources	2	Order product name	TPS762 C 2xTL5-28W HFP AC-MLO FU SMS
Optical cover type	Acrylate micro-lens optic	Full product name	TPS762 C 2xTL5-28W HFP AC-MLO FU SMS
Operating and Electrical		Full product code	911401006180
Input Voltage	220 to 240 V	Order code	911401006180
Line Frequency	50 to 60 Hz	Material Nr. (12NC)	911401006180
Power Consumption	28 W	Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8718291995098
		Numerator - Packs per outer box	1

Savio TPS760 C

EAN/UPC - Case	8718291995098
----------------	---------------

Dimensional drawing

