



Optivision MVP507 C

MVP507 CMHN-LA2000W/842 380-415V NB

MASTER MHN-LA, 2000 W, Narrow beam

An asymmetric luminaire for down lighting that combines a compact design with very high efficiency. It provides excellent spill-light control and limitation of glare and upward leakage of light. It accommodates metal-halide lamps for good color rendering or high-pressure sodium lamps for economical operation. Available with narrow, medium and wide beams.

Product data

General Information	
Lamp family code	MHN-LA [MASTER MHN-LA]
Gear	CONV [Conventional]
Light Technical	
Number of light sources	1
Light source color	842 neutral white
Optic type outdoor	Narrow beam
Operating and Electrical	
Input Voltage	380 to 415 V
Line Frequency	50 Hz
Power Consumption	2,000 W

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Product Data	
Order product name	MVP507 CMHN-LA2000W/842 380-415V NB
Full product name	MVP507 CMHN-LA2000W/842 380-415V NB
Full product code	911401042180
Order code	911401042180
Material Nr. (12NC)	911401042180
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Optivision MVP507 C

Dimensional drawing

