



ConTempo 150-250-350

RVP350 HPI-T250W K IC 220V-50Hz A SP

MASTER HPI-T Plus, 250 W, Asymmetrical

The Contempo floodlight has a registered design that blends well with contemporary outdoor environments. It has a rugged pressure die-casted aluminum housing with corrosion resistant powder coating. Contempo also features an integrated energy saving copper ballast, electronic semi-parallel ignitor and capacitor. The unit has passed rigorous tests for dust and water ingress protection.

Product data

| General Information | |
|--------------------------|----------------------------|
| Lamp family code | HPI-TP [MASTER HPI-T Plus] |
| Cap-Base | E40 [E40] |
| Gear | CONV [Conventional] |
| Light Technical | |
| Number of light sources | 1 |
| Optic type outdoor | Asymmetrical |
| Operating and Electrical | |
| Input Voltage | 220 V |
| Line Frequency | 50 Hz |
| Power Consumption | 250 W |
| Mechanical and Housing | |
| Housing Color | - |

| Approval and Application | |
|---------------------------------|--|
| Ingress protection code | IP65 [Dust penetration-protected, jet-proof] |
| Product Data | |
| Order product name | RVP350 HPI-T250W K IC 220V-50Hz A SP |
| Full product name | RVP350 HPI-T250W K IC 220V-50Hz A SP |
| Full product code | 911401058580 |
| Order code | 911401058580 |
| Material Nr. (12NC) | 911401058580 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 6923828621483 |
| Numerator - Packs per outer box | 1 |
| EAN/UPC - Case | 6923828621483 |

ConTempo 150-250-350

Dimensional drawing

