



# ConTempo 150-250-350

## RVP250 SON-T150W K IC 220V-50Hz A SP

SON-T, 150 W, Asymmetrical

The Contempo floodlight has a registered design that blends well with contemporary outdoor environments. It has a rugged pressure die-casted aluminum housing with corrosion resistant powder coating. Contempo also features an integrated energy saving copper ballast, electronic semi-parallel ignitor and capacitor. The unit has passed rigorous tests for dust and water ingress protection.

### Product data

| General Information      |                     |
|--------------------------|---------------------|
| Lamp family code         | SON-T [SON-T]       |
| Cap-Base                 | E40 [E40]           |
| Gear                     | CONV [Conventional] |
| Light Technical          |                     |
| Number of light sources  | 1                   |
| Optic type outdoor       | Asymmetrical        |
| Operating and Electrical |                     |
| Input Voltage            | 220 V               |
| Line Frequency           | 50 Hz               |
| Power Consumption        | 150 W               |
| Mechanical and Housing   |                     |
| Housing Color            | -                   |

| Approval and Application        |  |
|---------------------------------|--|
| Ingress protection code         | IP65 [Dust penetration-protected, jet-proof] |
| Product Data                    |  |
| Order product name              | RVP250 SON-T150W K IC 220V-50Hz A SP         |
| Full product name               | RVP250 SON-T150W K IC 220V-50Hz A SP         |
| Full product code               | 911401059380                                 |
| Order code                      | 911401059380                                 |
| Material Nr. (12NC)             | 911401059380                                 |
| Numerator - Quantity Per Pack   | 1  |
| EAN/UPC - Product/Case          | 6923828621414                                |
| Numerator - Packs per outer box | 1  |
| EAN/UPC - Case                  | 6923828621414                                |

## ConTempo 150-250-350

### Dimensional drawing

