



VerseBay HPK518

HPK518 1xHPI-P400W-BUS IC 220V-50Hz

1, MASTER HPI Plus, 400 W, 220 V, 50 Hz

Reliable, effective lighting in the industrial workplace is a crucial factor influencing productivity, safety and staff well-being. The VerseBay high-bay luminaire clearly embodies such lighting requirements. Its solid, quality construction and reliable performance excels even in the toughest working environments. Its specially designed beam regulator allows light distribution to be optimally set for a broad range of work areas using just a single reflector. VerseBay also embodies extraordinary features that dramatically eases installation and maintenance. An external waterproof connector makes installation faster than ever while its tool-less lamp replacement is quick and hassle-free. So whatever your high-bay lighting requirements – industrial areas, logistics centers or public spaces – VerseBay offers a host of innovative features that can add new dimensions to versatility and ease of installation.

Product data

General Information		Approval and Application	
Lamp family code	HPI-P [MASTER HPI Plus]	Protection class IEC	Safety class I
Gear	CONV [Conventional]		
Light Technical		Product Data	
Number of light sources	1	Order product name	HPK518 1xHPI-P400W-BUS IC 220V-50Hz
		Full product name	HPK518 1xHPI-P400W-BUS IC 220V-50Hz
		Full product code	911401089380
		Order code	911401089380
Operating and Electrical		Material Nr. (12NC)	911401089380
Input Voltage	220 V	Numerator - Quantity Per Pack	1
Line Frequency	50 Hz	Numerator - Packs per outer box	2
Power Consumption	400 W		

Dimensional drawing

