



EnduraBay HPK138/238

HPK138 1xHPI-P400W-BUS IC 220 50

1, MASTER HPI Plus, 400 W, 220 V, 50 Hz

HPK238's attractive and unobtrusive presence energizes your interior surroundings, assuring you functionality, safety and overall product performance. Its robust, dependable construction along with its ease of installation and maintenance truly make this highbay luminaire a durable, yet appealing solution. EnduraBay LX HPK138. Elegance and efficiency were the themes driving the design of EnduraBay LX. Its attractive yet unobtrusive presence energizes your interior surroundings, assuring you functionality, safety and overall product performance. What's more, it is easy on your budget. EnduraBay LX truly offers you peace of mind in your highbay installation. This robust luminaire makes it an impressive light source, as does its attractive minimalist design. The most striking feature of this high-bay luminaire is its four "shields" on the upper part of the housing, giving any lighting installation a distinctive elegance.

Product data

General Information		Line Frequency	
Lamp family code	HPI-P [MASTER HPI Plus]	Line Frequency	50 Hz
Cap-Base	E40 [E40]	Power Consumption	400 W
Gear	CONV [Conventional]	Approval and Application	
Light Technical		Protection class IEC	Safety class I
Number of light sources	1	Product Data	
Operating and Electrical		Order product name	HPK138 1xHPI-P400W-BUS IC 220 50
Input Voltage	220 V	Full product name	HPK138 1xHPI-P400W-BUS IC 220 50
		Full product code	692382863067600

EnduraBay HPK138/238

Order code	911401092180
Material Nr. (12NC)	911401092180
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828630676

Numerator - Packs per outer box	1
EAN/UPC - Case	6923828630676

Dimensional drawing

