



EnduraBay HPK138/238

HPK238 1xHPI-P250W-BU IC 220 50 BK

1, MASTER HPI Plus, 250 W, 220 V, 50 Hz, Black

HPK238's attractive and unobtrusive presence energizes your interior surroundings, assuring you functionality, safety and overall product performance. Its robust, dependable construction along with its ease of installation and maintenance truly make this highbay luminaire a durable, yet appealing solution. EnduraBay LX HPK138. Elegance and efficiency were the themes driving the design of EnduraBay LX. Its attractive yet unobtrusive presence energizes your interior surroundings, assuring you functionality, safety and overall product performance. What's more, it is easy on your budget. EnduraBay LX truly offers you peace of mind in your highbay installation. This robust luminaire makes it an impressive light source, as does its attractive minimalist design. The most striking feature of this high-bay luminaire is its four "shields" on the upper part of the housing, giving any lighting installation a distinctive elegance.

Product data

General Information		Line Frequency	
Lamp family code	HPI-P [MASTER HPI Plus]	Line Frequency	50 Hz
Cap-Base	E40 [E40]	Power Consumption	250 W
Gear	CONV [Conventional]	Mechanical and Housing	
Light Technical		Housing Color	Black
Number of light sources	1	Approval and Application	
Operating and Electrical		Protection class IEC	Safety class I
Input Voltage	220 V		

EnduraBay HPK138/238

Product Data	
Order product name	HPK238 1xHPI-P250W-BU IC 220 50 BK
Full product name	HPK238 1xHPI-P250W-BU IC 220 50 BK
Full product code	911401092880
Order code	911401092880

Material Nr. (12NC)	911401092880
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

