



GreenUp Highbay G2

BY560P LED105/CW PSU HRO

GreenUp Highbay G2, 75 W, 10500 lm, 6500 K, 45° x 90°

Height is not an issue any more, maximum 16m movement detection together with the wireless ZigBee control, GreenUp HighBay G2,light up your space smartly.

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
CE mark	CE mark
Warranty period	3 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	-
Glow-wire test	Temperature 650 °C, duration 5 s
Light Technical	
Luminous Flux	10,500 lm
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	140 lm/W
Color rendering index (CRI)	>80


Beam angle of light source	- degree(s)
Light source color	865 cool daylight
Optic type	High-rack optic
Optical cover type	Linear-lens array in polycarbonate cover
Luminaire light beam spread	45° x 90°
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	19 A
Inrush time	280 ms
Power Consumption	75 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	Cable 1.5 m without plug

GreenUp Highbay G2

Number of products on MCB of 16 A type	24
B	
Temperature	
Ambient temperature range	-20 to +45 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum extruded
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	Aluminum and white
Optical cover finish	Clear
Overall length	525 mm
Overall width	190 mm
Approval and Application	
Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.313.0.324)SDCM<5
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	0.01 %
Median useful life L70B50	65,000 hour(s)
Median useful life L80B50	45,000 hour(s)
Median useful life L90B50	25,000 hour(s)
Application Conditions	
Maximum dim level	Not applicable
Suitable for random switching	No
Product Data	
Order product name	BY560P LED105/CW PSU HRO
Full product name	BY560P LED105/CW PSU HRO
Full product code	911401503351
Order code	911401503351
Material Nr. (12NC)	911401503351
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

Dimensional drawing



GreenUp Highbay G2

