



GreenUp Highbay G2

BY560P LED160/CW PSU WB

GreenUp Highbay G2, 120 W, 16000 lm, 6500 K, 90°

Height is not an issue any more, maximum 16m movement detection together with the wireless ZigBee control, GreenUp HighBay G2,light up your space smartly.

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

Product data


General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
CE mark	CE mark
Warranty period	3 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	-
Glow-wire test	Temperature 650 °C, duration 5 s
Light Technical	
Luminous Flux	16,000 lm
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	133 lm/W
Color rendering index (CRI)	>80

Beam angle of light source	- degree(s)
Light source color	865 cool daylight
Optic type	Wide beam
Optical cover type	Linear-lens array in polycarbonate cover
Luminaire light beam spread	90°
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	46 A
Inrush time	440 ms
Power Consumption	120 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	Cable 1.5 m without plug

GreenUp Highbay G2

Number of products on MCB of 16 A type	11
B	
Temperature	
Ambient temperature range	-20 to +45 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum extruded
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	Aluminum and white
Optical cover finish	Clear
Overall length	405 mm
Overall width	280 mm
Approval and Application	
Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class I

Dimensional drawing



Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.313.0.324)SDCM<5
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	0.01 %
Median useful life L70B50	65,000 hour(s)
Median useful life L80B50	45,000 hour(s)
Median useful life L90B50	25,000 hour(s)
Application Conditions	
Maximum dim level	Not applicable
Suitable for random switching	No
Product Data	
Order product name	BY560P LED160/CW PSU WB
Full product name	BY560P LED160/CW PSU WB
Full product code	911401504351
Order code	911401504351
Material Nr. (12NC)	911401504351
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

GreenUp Highbay G2

