



CoreLine Highbay

BY121P G3 LED205S/840 PSD WB GR

CoreLine Highbay, 155 W, 20500 lm, 4000 K, DALI, 100°

Following the successful introduction of the CoreLine High-bay in 2013, the upgrade to a new generation of LEDs has further improved color rendering and total cost of ownership. Designed as a replacement for HPI 250/400 W luminaires, CoreLine High-bay offers customers all the benefits of LED lighting – fresh light quality, longer service lifetime, reduced energy consumption and maintenance – from a trusted manufacturer. At the same time, it delivers clear benefits for the installer too. The luminaire can be installed on the existing grid. Electrical connection is straightforward: there is no need to open the luminaire for installation or servicing. And being smaller and lighter than conventional luminaires, it is very easy to handle.

Product data

General Information		Warranty period	
Lamp family code	LED205S [LED module, system flux 20500 lm]	Flammability mark	For mounting on normally flammable surfaces
Light source replaceable	No	ENEC mark	-
Number of gear units	1 unit	Glow-wire test	Temperature 650 °C, duration 5 s
Driver included	Yes	EU RoHS compliant	Yes
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Light Technical	
Light source engine type	LED	Luminous Flux	20,500 lm
Service tag	Yes	Correlated Color Temperature (Nom)	4000 K
CE mark	CE mark	Luminous Efficacy (rated) (Nom)	130 lm/W
		Color rendering index (CRI)	≥80
		Number of light sources	1
		Beam angle of light source	- degree(s)
		Light source color	840 neutral white
		Optic type	Wide beam

CoreLine Highway

Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	100°

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Average CLO power consumption	142 W
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	155 W
Power Factor (Fraction)	0.9
Connection	Connection unit 3-pole
Cable	Cable 0.5 m with cable connector 3-pole
Number of products on MCB of 16 A type B	8

Temperature

Ambient temperature range	-30 to +45 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	Yes

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	Grey
Optical cover finish	Clear
Overall length	454 mm
Overall width	452 mm
Overall height	152 mm

Overall diameter	452 mm
Dimensions (Height x Width x Depth)	152 x 452 x 454 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L70


Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%
Suitable for random switching	Yes

Product Data

Order product name	BY121P G3 LED205S/840 PSD WB GR
Full product name	BY121P G3 LED205S/840 PSD WB GR
Full product code	871016330147100
Order code	30147100
Material Nr. (12NC)	911401505631
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163301471
Numerator - Packs per outer box	1
EAN/UPC - Case	8710163301471

Dimensional drawing



CoreLine Highbay

