




Greenperform Waterproof G2 - WT188C

WT169C LED20 CW L1200 PSU

Greenperform Waterproof G2 - WT188C, 18 W, 2000 lm, 6500 K

Greenperform Waterproof G2 luminaire and its components are designed for both indoor and semi-outdoor application (anti-UV PC material housing and diffuser, stainless steel installation accessory). We design for friendly optical, energy saving, reliable quality, and easy wiring. Beyond that, GreenParking wireless motion detective system is ready to provide the maximum energy saving and new lighting experience to you.

Product data

General Information		Operating and Electrical	
Light source engine type	LED	Input Voltage	220 to 240 V
CE mark	CE mark	Line Frequency	50 to 60 Hz
Light Technical		Power Consumption	18 W
Luminous Flux	2,000 lm	Power Factor (Fraction)	0.9
Correlated Color Temperature (Nom)	6500 K	Number of products on MCB of 16 A type B	24
Luminous Efficacy (rated) (Nom)	117 lm/W	Temperature	
Color rendering index (CRI)	>80	Ambient temperature range	-30 to +45 °C
Light source color	865 cool daylight	Controls and Dimming	
Optical cover type	Polycarbonate bowl/cover foggy	Dimmable	No

Greenperform Waterproof G2 - WT188C

Control interface	-
-------------------	---

Mechanical and Housing

Housing Material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Gray and white
Optical cover finish	Opal

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Power consumption tolerance	+/-10%
-----------------------------	--------

Product Data

Order product name	WT169C LED20 CW L1200 PSU
Full product name	WT169C LED20 CW L1200 PSU
Full product code	911401510141
Order code	911401510141
Material Nr. (12NC)	911401510141
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

