



# GreenSpace Surface-mounted

## SM295C LED68/865 PSU WP BK

GreenSpace Surface-mounted, 66 W, 6600 lm, 6500 K, High-gloss mirror, Dust penetration-protected, jet-proof

Philips GreenSpace Surface-mounted LED Downlight delivers a superior LED alternative that's up to 66% more energy efficient than the conventional downlight retrofits. Blending seamlessly into its environment, GreenSpace Surface-mounted LED Downlight mimics the form of conventional recessed downlights minus the associated high energy and maintenance costs. Philips GreenSpace Surface-mounted LED Downlight is also ideal for all commercial lighting applications as well as public indoor space where there is limited space in the ceiling.

### Product data


General Information		Color rendering index (CRI)	
Light source replaceable	No	Light source color	865 cool daylight
Number of gear units	1 unit	Optic type	High-gloss mirror
Driver included	Yes	Optical cover type	Reflector
Light source engine type	LED	Luminaire light beam spread	60°
Service tag	Yes	Operating and Electrical	
CE mark	CE mark	Input Voltage	220 to 240 V
Warranty period	3 years	Line Frequency	50 or 60 Hz
Glow-wire test	Temperature 750 °C, duration 5 s	Inrush current	25 A
Light Technical		Inrush time	0.202 ms
Luminous Flux	6,600 lm	Power Consumption	66 W
Correlated Color Temperature (Nom)	6500 K	Power Factor (Fraction)	0.9
Luminous Efficacy (rated) (Nom)	100 lm/W		

## GreenSpace Surface-mounted

Number of products on MCB of 16 A type B 24	
<b>Temperature</b>	
Ambient temperature range	-20 to +40 °C
<b>Controls and Dimming</b>	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
<b>Mechanical and Housing</b>	
Housing Material	Aluminum die cast
Reflector material	Aluminum
Optic material	Aluminum
Optical cover material	-
Housing Color	Black
Optical cover finish	-
Overall length	0 mm
Overall width	0 mm
Overall height	239 mm
Overall diameter	200 mm
Dimensions (Height x Width x Depth)	239 x 0 x 0 mm
<b>Approval and Application</b>	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK02 [0.2 J standard]

Protection class IEC	Safety class I
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.31, 0.32) SDCM<5
Power consumption tolerance	+/-10%
<b>Over Time Performance (IEC Compliant)</b>	
Driver failure rate at 5000 h	0.01 %
Median useful life L70B50	50,000 hour(s)
Median useful life L80B50	40,000 hour(s)
Median useful life L90B50	20,000 hour(s)
<b>Application Conditions</b>	
Maximum dim level	Not applicable
Suitable for random switching	No
<b>Product Data</b>	
Order product name	SM295C LED68/865 PSU WP BK
Full product name	SM295C LED68/865 PSU WP BK
Full product code	911401512331
Order code	911401512331
Material Nr. (12NC)	911401512331
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

### Dimensional drawing



## GreenSpace Surface-mounted

