



GreenPerform Troffer

RC100X LED37S 840 W30L120 IAO G3

GreenPerform Troffer, 116 lm/W, 840 neutral white, InterAct office

GreenPerform troffer improves the compact design of the last generation with performance improvement and more variants for different markets. Integrating with all available system: POE, InterAct office wireless, InterAct Office Pro, ActiLume controller, GreenPerform troffer offers additional energy saving and connected features.

Product data

General Information		Optical cover type	
Light source replaceable	No		Variable linear-lens array in polycarbonate cover
Number of gear units	1 unit		
Driver included	Yes	Operating and Electrical	
Light source engine type	LED	Input Voltage	220 to 240 V
Glow-wire test	Temperature 600 °C, duration 30 s	Line Frequency	50 to 60 Hz
Flammability mark	For mounting on normally flammable surfaces	Inrush current	21 A
CE mark	CE mark	Inrush time	280 ms
Warranty period	3 years	Power Consumption	32 W
		Power Factor (Fraction)	0.9
		Number of products on MCB of 16 A type B 21	
Light Technical		Temperature	
Luminous Flux	3,700 lm	Ambient temperature range	-20 to +40 °C
Correlated Color Temperature (Nom)	4000 K		
Luminous Efficacy (rated) (Nom)	116 lm/W	Controls and Dimming	
Color rendering index (CRI)	80	Dimmable	Yes
Light source color	840 neutral white	Control interface	InterAct office

GreenPerform Troffer

Constant light output	No
-----------------------	----

Mechanical and Housing

Housing Material	Metal
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White
Optical cover finish	Ribbed
Overall length	1,197 mm
Overall width	297 mm
Overall height	46 mm
Dimensions (Height x Width x Depth)	46 x 297 x 1197 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Initial chromaticity	SDCM<4
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
---------------------------	----------------

Application Conditions

Suitable for random switching	No
-------------------------------	----

Product Data

Order product name	RC100X LED37S 840 W30L120 IAO G3
Full product name	RC100X LED37S 840 W30L120 IAO G3
Full product code	911401512951
Order code	911401512951
Material Nr. (12NC)	911401512951
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

Dimensional drawing

