



# GreenPerform Troffer

## RC100B LED37S 840 W60L120 PSU OC CAU

GreenPerform Troffer, 129 lm/W, 840 neutral white

GreenPerform troffer improves the compact design of the last generation with performance improvement and more variants for different markets. Integrating with all available system: POE, InterAct office wireless, InterAct Office Pro, ActiLume controller, GreenPerform troffer offers additional energy saving and connected features.

### Product data

General Information		Operating and Electrical	
Light source replaceable	No	Input Voltage	220 to 240 V
Number of gear units	1 unit	Line Frequency	50 to 60 Hz
Driver included	Yes	Inrush current	3 A
Light source engine type	LED	Inrush time	62 ms
CE mark	CE mark	Power Consumption	32 W
Warranty period	3 years	Power Factor (Fraction)	0.9
Flammability mark	For mounting on normally flammable surfaces	Number of products on MCB of 16 A type B 24	
Glow-wire test	Temperature 600 °C, duration 30 s	Temperature	
Light Technical		Ambient temperature range	-20 to +40 °C
Luminous Flux	3,700 lm	Controls and Dimming	
Correlated Color Temperature (Nom)	4000 K	Dimmable	No
Luminous Efficacy (rated) (Nom)	129 lm/W	Control interface	-
Color rendering index (CRI)	80	Constant light output	No
Light source color	840 neutral white	Mechanical and Housing	
Optical cover type	Variable linear-lens array in polycarbonate cover	Housing Material	Metal
		Optic material	Polycarbonate

## GreenPerform Troffer

Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White
Optical cover finish	Ribbed
Overall length	1,197 mm
Overall width	597 mm
Overall height	46 mm
Dimensions (Height x Width x Depth)	46 x 597 x 1197 mm

### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<4
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 h
---------------------------	----------

### Application Conditions

Suitable for random switching	No
-------------------------------	----

### Product Data

Order product name	RC100B LED37S 840 W60L120 PSU OC CAU
Full product name	RC100B LED37S 840 W60L120 PSU OC CAU
Full product code	911401514251
Order code	911401514251
Material Nr. (12NC)	911401514251
Local order code	RC100B37460120P
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

## Dimensional drawing

