



PowerBalance RC600B

RC600B LED40S/840 POE W30L120 MA CAU

PowerBalance RC600B, 117.14 lm/W, 840 neutral white, Power over Ethernet

When it comes to lighting an office space with LED luminaires, people are willing to invest in sustainability, but only at reasonable cost. At the same time, the system should comply with office lighting norms to ensure a comfortable working environment. PowerBalance is an attractively priced LED luminaire specially developed to meet all office requirements. It consumes significantly less energy while offering longer life of the light source, resulting in lower operational cost compared to traditional luminaires.

Product data

General Information		Light Technical	
Light source replaceable	No	Luminous Flux	4,100 lm
Number of gear units	1 unit	Correlated Color Temperature (Nom)	4000 K
Driver included	Yes	Luminous Efficacy (rated) (Nom)	117.14 lm/W
Light source engine type	LED	Color rendering index (CRI)	>80
Service tag	Yes	Beam angle of light source	- degree(s)
Glow-wire test	Temperature 650 °C, duration 30 s	Light source color	840 neutral white
Flammability mark	-	Optic type	Beam angle 100°
CE mark	CE mark	Optical cover type	Polycarbonate
ENEC mark	ENEC mark	Luminaire light beam spread	120°
Warranty period	3 years	Operating and Electrical	
EU RoHS compliant	No	Input Voltage	220/240 V
		Line Frequency	50 to 60 Hz

PowerBalance RC600B

Power Consumption	35 W
Power Factor (Fraction)	0.9
Connection	Internal connector
Cable	-
Number of products on MCB of 16 A type B -	

Temperature

Ambient temperature range	0 to +40 °C
---------------------------	-------------

Controls and Dimming

Dimmable	Yes
Control interface	Power over Ethernet
Constant light output	No

Mechanical and Housing

Housing Material	Metal
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White
Optical cover finish	Opal
Overall length	297 mm
Overall width	1,197 mm
Overall height	69.7 mm
Dimensions (Height x Width x Depth)	70 x 1197 x 297 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
-------------------------	-------------------------

Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class III

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<4
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
---------------------------	----------------


Application Conditions

Maximum dim level	20%
Suitable for random switching	Yes

Product Data

Order product name	RC600B LED40S/840 POE W30L120 MA CAU
Full product name	RC600B LED40S/840 POE W30L120 MA CAU
Full product code	911401515341
Order code	911401515341
Material Nr. (12NC)	911401515341
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

Dimensional drawing



PowerBalance RC600B

