



# GreenPerform Highbay HT

## BY688P LED160/NW PSD WB G2 120-277XTEN

GreenPerform Highbay HT, 120 W, 16000 lm, 4000 K, DALI, 93°

GreenPerform Highbay High Ta is an ideal solution for high temperature application and special heavy industry, enables a safe working environment with leading specification and comfortable light. In the meanwhile, lower the overall maintenance cost eventually.

### Product data


General Information			
Light source replaceable	No	Beam angle of light source	- degree(s)
Number of gear units	1 unit	Light source color	840 neutral white
Driver included	Yes	Optic type	Wide beam
Light source engine type	LED	Optical cover type	Tempered glass
CE mark	CE mark	Luminaire light beam spread	93°
Warranty period	3 years	Operating and Electrical	
Flammability mark	For mounting on normally flammable surfaces	Input Voltage	120 to 277 V
ENEC mark	-	Line Frequency	50 to 60 Hz
Glow-wire test	Temperature 650 °C, duration 5 s	Inrush current	126 A
EU RoHS compliant	No	Inrush time	140 ms
Light Technical		Power Consumption	120 W
Luminous Flux	16,000 lm	Power Factor (Fraction)	0.95
Correlated Color Temperature (Nom)	4000 K	Connection	Flying leads/wires
Luminous Efficacy (rated) (Nom)	133 lm/W	Cable	Cable 0.3 m without plug
Color rendering index (CRI)	>80	Number of products on MCB of 16 A type B 8	

GreenPerform Highbay HT

Temperature	
Ambient temperature range	-30 to +60 °C
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum die cast
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Tempered glass
Fixation material	-
Housing Color	Silver
Optical cover finish	Clear
Overall height	150 mm
Overall diameter	456 mm
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Initial chromaticity	(0.38.0.38)SDCM<5
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	0.01 %
Median useful life L70B50	75,000 hour(s)
Median useful life L80B50	60,000 hour(s)
Median useful life L90B50	45,000 hour(s)
Application Conditions	
Maximum dim level	10% (depends on dimmer, ELV)
Suitable for random switching	No
Product Data	
Order product name	BY688P LED160/NW PSD WB G2 120-277XTEN
Full product name	BY688P LED160/NW PSD WB G2 120-277XTEN
Full product code	911401515551
Order code	911401515551
Material Nr. (12NC)	911401515551
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing



## GreenPerform Highbay HT

