



# PowerBalance RC600B

## RC600B LED40S/830 POE W60L60 SL IN

PowerBalance RC600B, 117.14 lm/W, 830 warm white, Power over Ethernet

When it comes to lighting an office space with LED luminaires, people are willing to invest in sustainability, but only at reasonable cost. At the same time, the system should comply with office lighting norms to ensure a comfortable working environment. PowerBalance is an attractively priced LED luminaire specially developed to meet all office requirements. It consumes significantly less energy while offering longer life of the light source, resulting in lower operational cost compared to traditional luminaires.

### Product data

General Information			
Light source replaceable	No	Correlated Color Temperature (Nom)	3000 K
Number of gear units	1 unit	Luminous Efficacy (rated) (Nom)	117.14 lm/W
Driver included	Yes	Color rendering index (CRI)	>80
Service tag	Yes	Beam angle of light source	- degree(s)
Glow-wire test	Temperature 650 °C, duration 30 s	Light source color	830 warm white
Flammability mark	-	Optic type	Beam angle 100°
CE mark	CE mark	Luminaire light beam spread	120°
ENEC mark	-	Operating and Electrical	
Warranty period	3 years	Input Voltage	220/240 V
EU RoHS compliant	No	Line Frequency	50 to 60 Hz
Light Technical		Power Consumption	35 W
Luminous Flux	4,100 lm	Power Factor (Fraction)	0.9
		Connection	Internal connector

## PowerBalance RC600B

Cable	-
Number of products on MCB of 16 A type B	-
<b>Temperature</b>	
Ambient temperature range	0 to +40 °C
<b>Controls and Dimming</b>	
Dimmable	Yes
Control interface	Power over Ethernet
Constant light output	No
<b>Mechanical and Housing</b>	
Housing Material	Metal
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White
Optical cover finish	Opal
Overall length	597 mm
Overall width	597 mm
Overall height	69.7 mm
Dimensions (Height x Width x Depth)	70 x 597 x 597 mm

<b>Approval and Application</b>	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class III
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<4
Power consumption tolerance	+/-10%
<b>Application Conditions</b>	
Maximum dim level	20%
Suitable for random switching	Yes
<b>Product Data</b>	
Order product name	RC600B LED40S/830 POE W60L60 SL IN
Full product name	RC600B LED40S/830 POE W60L60 SL IN
Full product code	911401515841
Order code	911401515841
Material Nr. (12NC)	911401515841
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

## Dimensional drawing

