



SmartBright Troffer

RC098V LED22S/865 W60L60 CPC

SmartBright Troffer, 94 lm/W, 865 cool daylight

SmartBright 2.0 troffer is the most affordable LED troffer delivering comfortable light with high quality. It offers two lumen options with three dimension types, 600x600, 300x1200 and 600x1200mm

Product data

Light Technical	
Luminous Flux	2,450 lm
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	94 lm/W
Color rendering index (CRI)	>80
Light source color	865 cool daylight
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	26 W
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Overall length	597 mm

Overall width	597 mm
Overall height	32 mm
Dimensions (Height x Width x Depth)	32 x 597 x 597 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Product Data	
Order product name	RC098V LED22S/865 W60L60 CPC
Full product name	RC098V LED22S/865 W60L60 CPC
Full product code	911401516021
Order code	911401516021
Material Nr. (12NC)	911401516021
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

SmartBright Troffer

Dimensional drawing

