



PowerBalance RC600B

RC600B LED40S/840 POE W60L60 SL IN

PowerBalance RC600B, 117.14 lm/W, 840 neutral white, Power over Ethernet

When it comes to lighting an office space with LED luminaires, people are willing to invest in sustainability, but only at reasonable cost. At the same time, the system should comply with office lighting norms to ensure a comfortable working environment. PowerBalance is an attractively priced LED luminaire specially developed to meet all office requirements. It consumes significantly less energy while offering longer life of the light source, resulting in lower operational cost compared to traditional luminaires.

Product data

General Information		Light Technical	
Light source replaceable	No	Luminous Flux	4,100 lm
Number of gear units	1 unit	Correlated Color Temperature (Nom)	4000 K
Driver included	Yes	Luminous Efficacy (rated) (Nom)	117.14 lm/W
Light source engine type	LED	Color rendering index (CRI)	>80
Service tag	Yes	Beam angle of light source	- degree(s)
Glow-wire test	Temperature 650 °C, duration 30 s	Light source color	840 neutral white
Flammability mark	-	Optic type	Beam angle 100°
CE mark	CE mark	Optical cover type	Opal
ENEC mark	-	Luminaire light beam spread	120°
Warranty period	3 years	Operating and Electrical	
EU RoHS compliant	No	Input Voltage	220/240 V
		Line Frequency	50 to 60 Hz

PowerBalance RC600B

Power Consumption	35 W
Power Factor (Fraction)	0.9
Connection	Internal connector
Cable	-
Number of products on MCB of 16 A type B	-
Temperature	
Ambient temperature range	0 to +40 °C
Controls and Dimming	
Dimmable	Yes
Control interface	Power over Ethernet
Constant light output	No
Mechanical and Housing	
Housing Material	Metal
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White
Optical cover finish	Opal
Overall length	597 mm
Overall width	597 mm
Overall height	69.7 mm
Dimensions (Height x Width x Depth)	70 x 597 x 597 mm

Dimensional drawing

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class III
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<4
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Median useful life L70B50	50,000 hour(s)
Application Conditions	
Maximum dim level	20%
Suitable for random switching	Yes
Product Data	
Order product name	RC600B LED40S/840 POE W60L60 SL IN
Full product name	RC600B LED40S/840 POE W60L60 SL IN
Full product code	911401516041
Order code	911401516041
Material Nr. (12NC)	911401516041
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

PowerBalance RC600B

