



# SmartBright Troffer

## RC098V LED44S/865 W60L120

SmartBright Troffer, 94 lm/W, 865 cool daylight

SmartBright 2.0 troffer is the most affordable LED troffer delivering comfortable light with high quality. It offers two lumen options with three dimension types, 600x600, 300x1200 and 600x1200mm

### Product data

Light Technical	
Luminous Flux	4,900 lm
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	94 lm/W
Color rendering index (CRI)	>80
Light source color	865 cool daylight
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	52 W
Controls and Dimming	
Dimmable	No
Constant light output	Yes
Mechanical and Housing	
Overall length	1,197 mm
Overall width	597 mm
Overall height	32 mm
Dimensions (Height x Width x Depth)	32 x 597 x 1197 mm

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Initial Performance (IEC Compliant)	
Initial chromaticity	(0.43, 0.40) SDCM>5
Application Conditions	
Maximum dim level	Not applicable
Product Data	
Order product name	RC098V LED44S/865 W60L120
Full product name	RC098V LED44S/865 W60L120
Full product code	911401516621
Order code	911401516621
Material Nr. (12NC)	911401516621
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

## SmartBright Troffer

### Dimensional drawing

