



GreenPerform Highbay HT

BY689P LED110/NW PSU NB G2 120-277XTEN

GreenPerform Highbay HT, 86 W, 11000 lm, 4000 K, 60°

GreenPerform Highbay High Ta is an ideal solution for high temperature application and special heavy industry, enables a safe working environment with leading speciation and comfortable light. In the meanwhile, lower the overall maintenance cost eventually.

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
CE mark	CE mark
Warranty period	3 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	-
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	No
Light Technical	
Luminous Flux	11,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	128 lm/W
Color rendering index (CRI)	>80


Beam angle of light source	- degree(s)
Light source color	840 neutral white
Optic type	Narrow beam
Optical cover type	Tempered glass
Luminaire light beam spread	60°
Operating and Electrical	
Input Voltage	120 to 277 V
Line Frequency	50 to 60 Hz
Inrush current	126 A
Inrush time	140 ms
Power Consumption	86 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	Cable 0.3 m without plug
Number of products on MCB of 16 A type B 8	

GreenPerform Highbay HT

Temperature	
Ambient temperature range	-30 to +60 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum die cast
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Tempered glass
Fixation material	-
Housing Color	Silver
Optical cover finish	Clear
Overall height	135 mm
Overall diameter	366 mm
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Initial chromaticity	(0.38.0.38)SDCM<5
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	0.01 %
Median useful life L70B50	75,000 hour(s)
Median useful life L80B50	60,000 hour(s)
Median useful life L90B50	45,000 hour(s)
Application Conditions	
Maximum dim level	Not applicable
Suitable for random switching	No
Product Data	
Order product name	BY689P LED110/NW PSU NB G2 120-277XTEN
Full product name	BY689P LED110/NW PSU NB G2 120-277XTEN
Full product code	911401517251
Order code	911401517251
Material Nr. (12NC)	911401517251
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing



GreenPerform Highbay HT

