



GreenUp Highbay G2

BY560X LED160/CW ACW2 IS WB

865 cool daylight - Power supply unit with DALI interface - Wide beam

Height is not an issue any more, maximum 16 m movement detection together with the wireless ZigBee control, GreenUp HighBay G2, light up your space smartly.

Product data

| General Information | |
|-------------------------------|--|
| Beam angle of light source | - ° |
| Lamp colour code | 865 cool daylight |
| Light source replaceable | No |
| Number of gear units | 1 unit |
| Driver/power unit/transformer | PSD [Power supply unit with DALI interface] |
| Driver included | Yes |
| Optic type | WB [Wide beam] |
| Luminaire light beam spread | 90° |
| Control interface | DALI |
| Connection | Flying leads/wires |
| Cable | Cable 1.5 m without plug (C1K5) |
| Protection class IEC | Safety class I (I) |
| Glow-wire test | 650/5 [Temperature 650 °C, duration 5 s] |
| Flammability mark | F [For mounting on normally flammable surfaces] |
| CE mark | CE mark |
| ENEC mark | - |
| Warranty period | 3 years |
| Constant light output | No |
| Number of products on MCB | 24 |

| Operating and Electrical | |
|-----------------------------|------------------------|
| Input voltage | 220-240 V |
| Input frequency | 50 to 60 Hz |
| Inrush current | 5.1 A |
| Inrush time | 760 ms |
| Power factor (min.) | 0.95 |
| Mechanical and Housing | |
| Housing material | Aluminum extruded |
| Reflector material | - |
| Optic material | Polycarbonate |
| Optical cover/lens material | Polycarbonate |
| Fixation material | - |
| Optical cover/lens finish | Clear |
| Overall length | 550 mm |
| Overall width | 280 mm |
| Colour | Aluminium and White |
| Approval and Application | |
| Ingress protection code | IP40 [Wire-protected] |

GreenUp Highway G2


| | |
|--|---------------------|
| Mech. impact protection code | IK03 [0.3 J] |
| Initial Performance (IEC Compliant) | |
| Initial luminous flux | 16000 lm |
| Luminous flux tolerance | +/-10% |
| Initial LED luminaire efficacy | 133 lm/W |
| Lamp colour temperature | 6500 K |
| Colour Rendering Index | >80 |
| Initial chromaticity | (0.313.0.324)SDCM<5 |
| Initial input power | 120 W |
| Power consumption tolerance | +/-10% |
| Over Time Performance (IEC Compliant) | |
| Median useful life L70B50 | 65000 h |
| Median useful life L80B50 | 45000 h |
| Median useful life L90B50 | 25000 h |

Application Conditions


| | |
|-------------------------------|---|
| Ambient temperature range | -20 to +45 °C |
| Maximum dimming level | 1% |
| Suitable for random switching | Yes (relates to presence/ movement detection and daylight harvesting) |

Product Data

| | |
|---------------------------------|-----------------------------|
| Full product code | 911401521451 |
| Order product name | BY560X LED160/CW ACW2 IS WB |
| Order code | 911401521451 |
| Numerator – quantity per pack | 1 |
| Numerator – packs per outer box | 2 |
| Material no. (12NC) | 911401521451 |
| Net weight (piece) | 2.899 kg |



Dimensional drawing



GreenUp High-bay BY550P/BY550X

