



GreenUp Highbay G2

BY560X LED160/CW ACW2 IS HRO

865 cool daylight - Power supply unit with DALI interface - High-rack optic

Height is not an issue any more, maximum 16 m movement detection together with the wireless ZigBee control, GreenUp HighBay G2, light up your space smartly.

Product data

General Information	
Beam angle of light source	- °
Lamp colour code	865 cool daylight
Light source replaceable	No
Number of gear units	1 unit
Driver/power unit/transformer	PSD [Power supply unit with DALI interface]
Driver included	Yes
Optic type	HRO [High-rack optic]
Luminaire light beam spread	45° x 90°
Control interface	DALI
Connection	Flying leads/wires
Cable	Cable 1.5 m without plug (C1K5)
Protection class IEC	Safety class I (I)
Glow-wire test	650/5 [Temperature 650 °C, duration 5 s]
Flammability mark	F [For mounting on normally flammable surfaces]
CE mark	CE mark
ENEC mark	-
Warranty period	3 years
Constant light output	No
Number of products on MCB	24

Operating and Electrical	
Input voltage	220-240 V
Input frequency	50 to 60 Hz
Inrush current	5.1 A
Inrush time	760 ms
Power factor (min.)	0.95
Mechanical and Housing	
Housing material	Aluminum extruded
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	-
Optical cover/lens finish	Clear
Overall length	550 mm
Overall width	280 mm
Colour	Aluminium and White
Approval and Application	
Ingress protection code	IP40 [Wire-protected]

GreenUp Highway G2


Mech. impact protection code	IK03 [0.3 J]
Initial Performance (IEC Compliant)	
Initial luminous flux	16000 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	133 lm/W
Lamp colour temperature	6500 K
Colour Rendering Index	>80
Initial chromaticity	(0.313.0.324)SDCM<5
Initial input power	120 W
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Median useful life L70B50	65000 h
Median useful life L80B50	45000 h
Median useful life L90B50	25000 h

Application Conditions


Ambient temperature range	-20 to +45 °C
Maximum dimming level	1%
Suitable for random switching	Yes (relates to presence/ movement detection and daylight harvesting)

Product Data

Full product code	911401521551
Order product name	BY560X LED160/CW ACW2 IS HRO
Order code	911401521551
Numerator – quantity per pack	1
Numerator – packs per outer box	2
Material no. (12NC)	911401521551
Net weight (piece)	2.899 kg



Dimensional drawing



GreenUp High-bay BY550P/BY550X

