



SlimBalance

RC550B LED40S 840 L120 PSU SD GM

SlimBalance, 97.56 lm/W, 840 neutral white

SlimBalance is a full range of product family with sleek and elegant design helps to create attractive and differentiated space for customers. The family covers different length (600mm, 1200mm, 1500mm), different end cap (round, square) and different light distribution (direct, indirect). Its office compliant version delivers comfortable light with good quality.

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

Product data

General Information		Operating and Electrical	
Light source replaceable	No	Correlated Color Temperature (Nom)	4000 K
Number of gear units	1 unit	Luminous Efficacy (rated) (Nom)	97.56 lm/W
Driver included	Yes	Color rendering index (CRI)	>80
Light source engine type	LED	Beam angle of light source	- degree(s)
CE mark	CE mark	Light source color	840 neutral white
Warranty period	3 years	Optic type	Wide beam
Flammability mark	-	Optical cover type	Opal
ENEC mark	-	Luminaire light beam spread	120°
Glow-wire test	Temperature 650 °C, duration 30 s		
EU RoHS compliant	Yes	Input Voltage	220/240 V
		Line Frequency	50 to 60 Hz
		Inrush current	19 A
		Inrush time	280 ms
Light Technical			
Luminous Flux	4,000 lm		

SlimBalance

Power Consumption	41 W
Power Factor (Fraction)	0.9
Connection	Flying leads/wires
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	-
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum extruded
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	Silver
Optical cover finish	Opal
Overall length	1,230 mm
Overall width	70 mm
Overall height	105 mm
Dimensions (Height x Width x Depth)	105 x 70 x 1230 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM< 3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
---------------------------	----------------

Application Conditions

Maximum dim level	Not applicable
-------------------	----------------

Product Data

Order product name	RC550B LED40S 840 L120 PSU SD GM
Full product name	RC550B LED40S 840 L120 PSU SD GM
Full product code	872016952126199
Order code	911401523141
Material Nr. (12NC)	911401523141
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169521261
Numerator - Packs per outer box	2
EAN/UPC - Case	8720169521261

Dimensional drawing



