



Celino LED BCS680 C

BCS680 C LED24/840 PSU W7L120 O-PC

LED Module 2400 lm, 840 neutral white, Power supply unit (On/Off), Opal diffuser in polycarbonate cover

Celino is a complete luminaire range that reflects the market trend towards miniaturisation and architectural integration, while delivering a significant advance in optical performance. Celino features Philips' aluminium micro optic with 3D lamellae, which ensures optimum visual comfort and efficiency in compliance with the latest office-lighting norm (EN 12464-1). Made of natural anodised aluminium, the housing of Celino is a mere 71 mm wide and has die-cast-aluminium end caps. The design allows multiple luminaires to be connected in a line arrangement. Celino is available as a full range – suspended, surface-mounted, free-standing and wall-mounted, with a choice of TL5, TL5 Eco or LED light sources – for maximum freedom in application.

Product data

General Information		Light Technical	
Lamp family code	LED24 [LED Module 2400 lm]	Luminous Flux	2,100 lm
Light source replaceable	No	Correlated Color Temperature (Nom)	4000 K
Number of gear units	1 unit	Luminous Efficacy (rated) (Nom)	71 lm/W
Driver included	Yes	Color rendering index (CRI)	>80
CE mark	-	Beam angle of light source	120 degree(s)
Warranty period	3 years	Light source color	840 neutral white
Flammability mark	-	Optic type	Wide beam
ENEC mark	-	Optical cover type	Opal diffuser in polycarbonate cover
Glow-wire test	Temperature 650 °C, duration 30 s	Luminaire light beam spread	110° x 110°
EU RoHS compliant	No	Operating and Electrical	
		Input Voltage	220-240 V

Celino LED BCS680 C

Line Frequency	50 to 60 Hz
Initial CLO power consumption	32 W
Average CLO power consumption	32 W
Inrush current	22 A
Inrush time	0.25 ms
Power Consumption	32 W
Power Factor (Fraction)	0.9
Connection	External connector
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	Yes

Mechanical and Housing

Housing Material	Aluminum extruded
Reflector material	Aluminum
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Silver
Optical cover finish	Opal
Overall length	1,120 mm
Overall width	71 mm
Overall height	76 mm
Dimensions (Height x Width x Depth)	76 x 71 x 1120 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7.5%
Initial chromaticity	(0.38, 0.38) SDCM <4
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	1 %
Median useful life L70B50	50,000 hour(s)
Median useful life L80B50	45,000 hour(s)
Median useful life L90B50	20,000 hour(s)


Application Conditions

Suitable for random switching	No
-------------------------------	----

Product Data

Order product name	BCS680 C LED24/840 PSU W7L120 O-PC
Full product name	BCS680 C LED24/840 PSU W7L120 O-PC
Full product code	911401539101
Order code	911401539101
Material Nr. (12NC)	911401539101
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing



Celino LED BCS680 C

