



# LuxSpace G4

## DN589B LED10/840 PSU C D150 WH WB WP GM

LuxSpace G4, 8.4 W, 1000 lm, 4000 K, Facetted reflector with beam angle 60°, Textured, Finger-protected; dust accumulation-protected, splash-proof

LuxSpace Gen4 is the a new LED downlight range combining light comfort and leading performance with luxury looking

### Product data

General Information		Optical cover type	
Light source replaceable	No	Reflector	
Number of gear units	1 unit	Operating and Electrical	
Driver included	Yes	Input Voltage	220 to 240 V
Light source engine type	LED	Line Frequency	50 or 60 Hz
CE mark	CE mark	Inrush current	5.2 A
Warranty period	3 years	Inrush time	0.23 ms
Flammability mark	For mounting on normally flammable surfaces	Power Consumption	8.4 W
Glow-wire test	Temperature 650 °C, duration 30 s	Power Factor (Fraction)	0.9
EU RoHS compliant	Yes	Connection	Push-in connector and pull relief
		Number of products on MCB of 16 A type B 34	
Light Technical		Temperature	
Luminous Flux	1,000 lm	Ambient temperature range	-20 to +40 °C
Correlated Color Temperature (Nom)	4000 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	119 lm/W	Dimmable	No
Color rendering index (CRI)	>80	Driver/power unit/transformer	Power supply unit external (On/Off)
Light source color	840 neutral white	Control interface	-
Optic type	Facetted reflector with beam angle 60°		

# LuxSpace G4

Constant light output	No
-----------------------	----

## Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White and black
Optical cover finish	Textured
Overall length	0 mm
Overall width	0 mm
Overall height	100 mm
Overall diameter	162 mm
Dimensions (Height x Width x Depth)	100 x 0 x 0 mm

## Approval and Application

Ingress protection code	IP20/54 [Finger-protected; dust accumulation-protected, splash-proof]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class II

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

## Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	1 %
Median useful life L70B50	50,000 hour(s)
Median useful life L80B50	50,000 hour(s)
Median useful life L90B50	21,000 hour(s)


## Application Conditions

Maximum dim level	Not applicable
-------------------	----------------

## Product Data

Order product name	DN589B LED10/840 PSU C D150 WH WB WP GM
Full product name	DN589B LED10/840 PSU C D150 WH WB WP GM
Full product code	872016972786100
Order code	911401549841
Material Nr. (12NC)	911401549841
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169727861
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169727861

## Dimensional drawing



## LuxSpace G4

