



LuxSpace G4

DN589B LED10/830 PSD C D150 WH WB WP GM

LuxSpace G4, 8.4 W, 940 lm, 3000 K, DALI, Facetted reflector with beam angle 60°, Textured, Finger-protected; dust accumulation-protected, splash-proof

LuxSpace Gen4 is the a new LED downlight range combining light comfort and leading performance with luxury looking

Product data

General Information		Optical cover type	
Light source replaceable	No	Reflector	
Number of gear units	1 unit	Operating and Electrical	
Driver included	Yes	Input Voltage	220 to 240 V
Light source engine type	LED	Line Frequency	50 or 60 Hz
Glow-wire test	Temperature 650 °C, duration 30 s	Inrush current	16 A
Flammability mark	For mounting on normally flammable surfaces	Inrush time	0.22 ms
CE mark	CE mark	Power Consumption	8.4 W
Warranty period	3 years	Power Factor (Fraction)	0.9
EU RoHS compliant	Yes	Connection	Connector with 2 additional wires for light regulation
Light Technical		Number of products on MCB of 16 A type B 24	
Luminous Flux	940 lm	Temperature	
Correlated Color Temperature (Nom)	3000 K	Ambient temperature range	-20 to +40 °C
Luminous Efficacy (rated) (Nom)	112 lm/W	Controls and Dimming	
Color rendering index (CRI)	>80	Dimmable	Yes
Light source color	830 warm white	Driver/power unit/transformer	Power supply unit external (On/Off)
Optic type	Facetted reflector with beam angle 60°	Control interface	DALI

LuxSpace G4

Constant light output	No
-----------------------	----

Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White and black
Optical cover finish	Textured
Overall length	0 mm
Overall width	0 mm
Overall height	100 mm
Overall diameter	162 mm
Dimensions (Height x Width x Depth)	100 x 0 x 0 mm

Approval and Application

Ingress protection code	IP20/54 [Finger-protected; dust accumulation-protected, splash-proof]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Power consumption tolerance	+/-10%
-----------------------------	--------

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	1 %
Median useful life L70B50	50,000 hour(s)
Median useful life L80B50	50,000 hour(s)
Median useful life L90B50	21,000 hour(s)

Application Conditions

Maximum dim level	1%
-------------------	----

Product Data

Order product name	DN589B LED10/830 PSD C D150 WH WB WP GM
Full product name	DN589B LED10/830 PSD C D150 WH WB WP GM
Full product code	911401550641
Order code	911401550641
Material Nr. (12NC)	911401550641
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

