



StyleState

ST916T LED20/930 PSU 1C WB BK

StyleState, 28.5 W, Premium white with CRI ≥ 90 , 34°, Finger-protected

Philips StyleState LED accent applies for gorgeous and delightful compact design with multiple color combination options, which could customize dedicated color or LOGO for customers. It is very flexible and compact solution. The installation mode could be also customized according to customer request, to apply for surface mount, angled surface, track or recessed etc, to satisfy different layout & display application requirement. Philips StyleState LED accent applies for professional lens, optical design and advanced LED technology, which could provide excellent light quality, color rendering and punch effect. It has 3 types of beam angle to satisfy different photometric requirement. It could customize dedicated color or LOGO for customers. The magnetic component and compact design provide infinite possibilities for customers.

Product data

General Information		Light Technical	
Light source replaceable	No	Luminous Flux	1,800 lm
Number of gear units	1 unit	Correlated Color Temperature (Nom)	3000 K
Driver included	Yes	Luminous Efficacy (rated) (Nom)	63.16 lm/W
Light source engine type	LED	Color rendering index (CRI)	>90
CE mark	CE mark	Beam angle of light source	- degree(s)
Warranty period	3 years	Light source color	Premium white with CRI ≥ 90
Flammability mark	-	Optic type	-
ENEC mark	-	Optical cover type	Lens
Glow-wire test	Temperature 600 °C, duration 30 s	Luminaire light beam spread	34°
EU RoHS compliant	Yes		

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	28.5 W
Power Factor (Fraction)	0.9
Connection	External connector
Cable	-
Number of products on MCB of 16 A type B	-

Temperature	
Ambient temperature range	-15 to +35 °C

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Electronic transformer
Control interface	-
Constant light output	No

Mechanical and Housing	
Housing Material	Aluminum
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Polymethyl methacrylate
Fixation material	Aluminum
Housing Color	Black
Optical cover finish	Textured
Overall length	0 mm
Overall width	0 mm
Overall height	175 mm
Overall diameter	60 mm

Dimensions (Height x Width x Depth)	175 x 0 x 0 mm
-------------------------------------	----------------

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM< 3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)	
Median useful life L70B50	50,000 hour(s)

Application Conditions	
Maximum dim level	Not applicable
Suitable for random switching	No

Product Data	
Order product name	ST916T LED20/930 PSU 1C WB BK
Full product name	ST916T LED20/930 PSU 1C WB BK
Full product code	911401555931
Order code	911401555931
Material Nr. (12NC)	911401555931
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing



