



GreenSpace Downlight G4

DN290B 1xDLED-3000 PSU ALU

GreenSpace Downlight G4, 6.5 W, Beam angle 60 to 120°,
Finger-protected

GreenSpace Gen4 is the new LED downlight with high efficacy (95~ 100lm/W) delivering substantial energy saving. It offers diverse configurations within 600~2,000lm. GreenSpace Gen4 could apply to shopping mall, retail store and office application with different variants . The lifetime is 50,000 hours (L70 @ 25C)

Product data

General Information		Power Factor (Fraction)		0.9	
Light source replaceable	No	Temperature			
Number of gear units	1 unit	Ambient temperature range	-20 to +40 °C		
CE mark	CE mark	Controls and Dimming			
ENEC mark	-	Dimmable	No		
Glow-wire test	Temperature 650 °C, duration 30 s	Driver/power unit/transformer	Power supply unit (On/Off)		
Light Technical		Constant light output	Yes		
Number of light sources	1	Mechanical and Housing			
Light source color	830 warm white	Housing Material	Aluminum		
Optic type	Beam angle 60 to 120°	Reflector material	Polycarbonate		
Optical cover type	Transparent bowl with white cover	Optic material	Polycarbonate		
Luminaire light beam spread	90°	Approval and Application			
Operating and Electrical		Ingress protection code	IP20 [Finger-protected]		
Input Voltage	220-240 V				
Power Consumption	6.5 W				



GreenSpace Downlight G4

Mech. impact protection code	IK02 [0.2 J standard]
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Median useful life L70B50	50,000 hour(s)
Product Data	
Full product code	911401564021

Order product name	DN290B 1xDLED-3000 PSU ALU
Order code	911401564021
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	36
Material Nr. (12NC)	911401564021
Full product name	DN290B 1xDLED-3000 PSU ALU

Dimensional drawing

Dimension 灯具尺寸	A (mm)	B (mm)
DN290B 1xDLED / ALU	95 / 99	∅ 122
DN291B 1xDLED / ALU	105 / 109	∅ 167
DN292B 1xDLED / ALU	114 / 118	∅ 218
DN293B 1xDLED / ALU	114 / 118	∅ 218



Dimension 灯具尺寸	A (mm)	B (mm)
DN290B 1xDLED / ALU	95 / 99	∅ 122
DN291B 1xDLED / ALU	105 / 109	∅ 167
DN292B 1xDLED / ALU	114 / 118	∅ 218
DN293B 1xDLED / ALU	114 / 118	∅ 218

