



# GreenSpace Downlight G4

## DN290B 1xDLED-4000 PSU WH

GreenSpace Downlight G4, 6.5 W, 4000 K, Beam angle 60 to 120°, Finger-protected

GreenSpace Gen4 is the new LED downlight with high efficacy (95~ 100lm/W) delivering substantial energy saving. It offers diverse configurations within 600~2,000lm. GreenSpace Gen4 could apply to shopping mall, retail store and office application with different variants . The lifetime is 50,000 hours (L70 @ 25C)

### Product data

| General Information                |                                   |
|------------------------------------|-----------------------------------|
| Light source replaceable           | No                                |
| Number of gear units               | 1 unit                            |
| CE mark                            | CE mark                           |
| ENEC mark                          | -                                 |
| Glow-wire test                     | Temperature 650 °C, duration 30 s |
| Light Technical                    |                                   |
| Correlated Color Temperature (Nom) | 4000 K                            |
| Number of light sources            | 1                                 |
| Light source color                 | 840 neutral white                 |
| Optic type                         | Beam angle 60 to 120°             |
| Optical cover type                 | Transparent bowl with white cover |
| Luminaire light beam spread        | 90°                               |
| Operating and Electrical           |                                   |
| Input Voltage                      | 220-240 V                         |

| Power Consumption             | 6.5 W                      |
|-------------------------------|----------------------------|
| Power Factor (Fraction)       | 0.9                        |
| Temperature                   |                            |
| Ambient temperature range     | -20 to +40 °C              |
| Controls and Dimming          |                            |
| Dimmable                      | No                         |
| Driver/power unit/transformer | Power supply unit (On/Off) |
| Constant light output         | Yes                        |
| Mechanical and Housing        |                            |
| Housing Material              | Aluminum                   |
| Reflector material            | Polycarbonate              |
| Optic material                | Polycarbonate              |

# GreenSpace Downlight G4

|                                     |                           |
|-------------------------------------|---------------------------|
| Approval and Application            |                           |
| Ingress protection code             | IP20 [Finger-protected]   |
| Mech. impact protection code        | IK02 [0.2 J standard]     |
| Initial Performance (IEC Compliant) |                           |
| Luminous flux tolerance             | +/-10%                    |
| Power consumption tolerance         | +/-10%                    |
| Product Data                        |                           |
| Order product name                  | DN290B 1xDLED-4000 PSU WH |

|                                 |                           |
|---------------------------------|---------------------------|
| Full product name               | DN290B 1xDLED-4000 PSU WH |
| Full product code               | 911401564421              |
| Order code                      | 911401564421              |
| Material Nr. (12NC)             | 911401564421              |
| Numerator - Quantity Per Pack   | 1                         |
| Numerator - Packs per outer box | 36                        |

## Dimensional drawing

