



GreenSpace Downlight G4

DN291B 1xDLED-4000 PSU ALU

GreenSpace Downlight G4, 11.6 W, 4000 K, Beam angle 60 to 120°, Finger-protected

GreenSpace Gen4 is the new LED downlight with high efficacy (95~ 100lm/W) delivering substantial energy saving. It offers diverse configurations within 600~2,000lm. GreenSpace Gen4 could apply to shopping mall, retail store and office application with different variants . The lifetime is 50,000 hours (L70 @ 25C)

Product data

General Information		Power Consumption	
Light source replaceable	No	11.6 W	
Number of gear units	1 unit	Power Factor (Fraction)	
CE mark	CE mark	0.9	
ENEC mark	-	Temperature	
Glow-wire test	Temperature 650 °C, duration 30 s	Ambient temperature range	
Light Technical		-20 to +40 °C	
Correlated Color Temperature (Nom)	4000 K	Controls and Dimming	
Number of light sources	1	Dimmable	
Light source color	840 neutral white	No	
Optic type	Beam angle 60 to 120°	Driver/power unit/transformer	
Optical cover type	Transparent bowl with white cover	Power supply unit (On/Off)	
Luminaire light beam spread	90°	Constant light output	
Operating and Electrical		Yes	
Input Voltage	220-240 V	Mechanical and Housing	
		Housing Material	
		Aluminum	
		Reflector material	
		Polycarbonate	
		Optic material	
		Polycarbonate	

GreenSpace Downlight G4

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]



Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data	
Order product name	DN291B 1xDLED-4000 PSU ALU

Full product name	DN291B 1xDLED-4000 PSU ALU
Full product code	911401564721
Order code	911401564721
Material Nr. (12NC)	911401564721
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	24

Dimensional drawing

Dimension 灯具尺寸	A (mm)	B (mm)
DN290B 1xDLED / ALU	95 / 99	Φ 122
DN291B 1xDLED / ALU	105 / 109	Φ 167
DN292B 1xDLED / ALU	114 / 118	Φ 218
DN293B 1xDLED / ALU	114 / 118	Φ 218



Dimension 灯具尺寸	A (mm)	B (mm)
DN290B 1xDLED / ALU	95 / 99	Φ 122
DN291B 1xDLED / ALU	105 / 109	Φ 167
DN292B 1xDLED / ALU	114 / 118	Φ 218
DN293B 1xDLED / ALU	114 / 118	Φ 218

