



GreenSpace Downlight G4

DN291B 1xDLED-6500 PSU ALU

GreenSpace Downlight G4, 11.6 W, 6500 K, Beam angle 60 to 120°, Finger-protected

GreenSpace Gen4 is the new LED downlight with high efficacy (95~ 100lm/W) delivering substantial energy saving. It offers diverse configurations within 600~2,000lm. GreenSpace Gen4 could apply to shopping mall, retail store and office application with different variants . The lifetime is 50,000 hours (L70 @ 25C)

Product data

General Information		Power Consumption	
Light source replaceable	No	Power Consumption	11.6 W
Number of gear units	1 unit	Power Factor (Fraction)	0.9
CE mark	CE mark	Temperature	
ENEC mark	-	Ambient temperature range	-20 to +40 °C
Glow-wire test	Temperature 650 °C, duration 30 s	Controls and Dimming	
Light Technical		Dimmable	No
Correlated Color Temperature (Nom)	6500 K	Driver/power unit/transformer	Power supply unit (On/Off)
Number of light sources	1	Constant light output	Yes
Light source color	865 cool daylight	Mechanical and Housing	
Optic type	Beam angle 60 to 120°	Housing Material	Aluminum
Optical cover type	Transparent bowl with white cover	Reflector material	Polycarbonate
Luminaire light beam spread	90°	Optic material	Polycarbonate
Operating and Electrical			
Input Voltage	220-240 V		

GreenSpace Downlight G4

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	DN291B 1xDLED-6500 PSU ALU
--------------------	----------------------------

Full product name	DN291B 1xDLED-6500 PSU ALU
-------------------	----------------------------

Full product code	911401564821
-------------------	--------------

Order code	911401564821
------------	--------------



Material Nr. (12NC)	911401564821
---------------------	--------------

Numerator - Quantity Per Pack	1
-------------------------------	---

Numerator - Packs per outer box	24
---------------------------------	----

Dimensional drawing

Dimension 灯具尺寸	A (mm)	B (mm)
DN290B 1xDLED / ALU	95 / 99	Φ 122
DN291B 1xDLED / ALU	105 / 109	Φ 167
DN292B 1xDLED / ALU	114 / 118	Φ 218
DN293B 1xDLED / ALU	114 / 118	Φ 218



Dimension 灯具尺寸	A (mm)	B (mm)
DN290B 1xDLED / ALU	95 / 99	Φ 122
DN291B 1xDLED / ALU	105 / 109	Φ 167
DN292B 1xDLED / ALU	114 / 118	Φ 218
DN293B 1xDLED / ALU	114 / 118	Φ 218

