



# GreenSpace Downlight G4

## DN290B 1xDLED-3000 PSU ALU CAU

GreenSpace Downlight G4, 6.5 W, Beam angle 60 to 120°,  
Finger-protected

GreenSpace Gen4 is the new LED downlight with high efficacy (95~ 100lm/W) delivering substantial energy saving. It offers diverse configurations within 600~2,000lm. GreenSpace Gen4 could apply to shopping mall, retail store and office application with different variants . The lifetime is 50,000 hours (L70 @ 25C)

### Product data

General Information		Power Factor (Fraction)		0.9
Light source replaceable	No	Cable	Cord with plug SAA 3-pole	
Number of gear units	1 unit	<b>Temperature</b>		
CE mark	CE mark	Ambient temperature range	-20 to +40 °C	
ENEC mark	-	<b>Controls and Dimming</b>		
Glow-wire test	Temperature 650 °C, duration 30 s	Dimmable	No	
<b>Light Technical</b>		Driver/power unit/transformer	Power supply unit (On/Off)	
Number of light sources	1	Constant light output	Yes	
Light source color	830 warm white	<b>Mechanical and Housing</b>		
Optic type	Beam angle 60 to 120°	Housing Material	Aluminum	
Optical cover type	Transparent bowl with white cover	Reflector material	Polycarbonate	
Luminaire light beam spread	90°	Optic material	Polycarbonate	
<b>Operating and Electrical</b>				
Input Voltage	220-240 V			
Power Consumption	6.5 W			

# GreenSpace Downlight G4

## Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%



## Product Data

Order product name	DN290B 1xDLED-3000 PSU ALU CAU
--------------------	--------------------------------

Full product name	DN290B 1xDLED-3000 PSU ALU CAU
Full product code	871016330039999
Order code	911401568221
Material Nr. (12NC)	911401568221
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163300399
Numerator - Packs per outer box	36

## Dimensional drawing

Dimension 灯具尺寸	A (mm)	B (mm)
DN290B 1xDLED / ALU	95 / 99	∅ 122
DN291B 1xDLED / ALU	105 / 109	∅ 167
DN292B 1xDLED / ALU	114 / 118	∅ 218
DN293B 1xDLED / ALU	114 / 118	∅ 218



Dimension 灯具尺寸	A (mm)	B (mm)
DN290B 1xDLED / ALU	95 / 99	∅ 122
DN291B 1xDLED / ALU	105 / 109	∅ 167
DN292B 1xDLED / ALU	114 / 118	∅ 218
DN293B 1xDLED / ALU	114 / 118	∅ 218

