



# CoreLine Highbay

## BY121P G3 LED205S/840 PIR WB GR

LED module, system flux 20500 lm, 840 neutral white, Power supply unit (On/Off), Wide beam, Grey

Following the successful introduction of the CoreLine High-bay in 2013, the upgrade to a new generation of LEDs has further improved color rendering and total cost of ownership. Designed as a replacement for HPI 250/400 W luminaires, CoreLine High-bay offers customers all the benefits of LED lighting – fresh light quality, longer service lifetime, reduced energy consumption and maintenance – from a trusted manufacturer. At the same time, it delivers clear benefits for the installer too. The luminaire can be installed on the existing grid. Electrical connection is straightforward: there is no need to open the luminaire for installation or servicing. And being smaller and lighter than conventional luminaires, it is very easy to handle.

### Product data

General Information		Lighting Technology	
Lamp family code	LED205S [LED module, system flux 20500 lm]	CE mark	CE mark
Light source replaceable	No	Warranty period	3 years + 2 years upon registration
Number of gear units	1 unit	Flammability mark	For mounting on normally flammable surfaces
Driver included	Yes	ENEC mark	-
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Glow-wire test	Temperature 650 °C, duration 5 s
Light source engine type	LED	EU RoHS compliant	Yes
Service tag	Yes	Light Technical	
		Luminous Flux	20,500 lm
		Correlated Color Temperature (Nom)	4000 K
		Luminous Efficacy (rated) (Nom)	130 lm/W
		Color rendering index (CRI)	≥80

CoreLine Highbay

Number of light sources	1
Beam angle of light source	- degree(s)
Light source color	840 neutral white
Optic type	Wide beam
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	100°

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	155 W
Power Factor (Fraction)	0.9
Connection	Connection unit 3-pole
Cable	Cable 0.5 m with cable connector 3-pole
Number of products on MCB of 16 A type B	8

Temperature

Ambient temperature range	-30 to +45 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	Grey
Optical cover finish	Clear
Overall length	454 mm
Overall width	452 mm

Overall height	152 mm
Overall diameter	452 mm
Dimensions (Height x Width x Depth)	152 x 452 x 454 mm

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L70

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	25%
Suitable for random switching	Yes

Product Data

Order product name	BY121P G3 LED205S/840 PIR WB GR
Full product name	BY121P G3 LED205S/840 PIR WB GR
Full product code	871016331714400
Order code	31714400
Material Nr. (12NC)	911401571241
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163317144
Numerator - Packs per outer box	1
EAN/UPC - Case	8710163317144

Dimensional drawing



