



Coreline Highbay Gen4

BY122P G4 LED250S/865 PSU NB

865 cool daylight - Power supply unit - Narrow beam - Grey

Following the success of the previous-generation CoreLine High-bay, the upgrade to a new generation further improves performance with new innovation design and provides higher efficiency, longer lifetime (to further improve the total cost of ownership) and optional DALI dimming for even further savings. Designed as a replacement for HPI 250/400 W luminaires, CoreLine High-bay G4 offers customers all the benefits of LED lighting – fresh light quality, longer service lifetime, reduced energy consumption and less maintenance – from a trusted manufacturer. At the same time, it delivers clear benefits for the installer too. The luminaire can be installed on the existing grid; electrical connection is straightforward – there is no need to open the luminaire for installation or servicing; and being smaller and lighter than conventional luminaires, it is very easy to handle

Product data

General Information			
Beam angle of light source	55°	Connection	Connection unit 3-pole
Light source colour	865 cool daylight	Cable	Cable 0.3 m with connector 3-pole
Light source replaceable	No	Protection class IEC	Safety class I
Number of gear units	1 unit	Glow-wire test	Temperature 650 °C, duration 30 s
Driver/power unit/transformer	PSU [Power supply unit]	Flammability mark	F [For mounting on normally flammable surfaces]
Driver included	Yes	CE mark	CE mark
Optic type	NB [Narrow beam]	ENEC mark	-
Optical cover/lens type	PC [Polycarbonate bowl/cover]	Warranty period	5 years
Luminaire light beam spread	55°	Constant light output	No
Control interface	-	Number of products on MCB	8

Coreline Highbay Gen4

RoHS mark	RoHS mark
Unified glare rating CEN	22

Operating and Electrical

Input voltage	220 to 240 V
Input frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	64 A
Inrush time	0.75 ms
Power factor (min.)	0.95

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing material	Aluminium
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	-
Optical cover/lens finish	Clear
Overall height	90 mm
Overall diameter	510 mm
Colour	Grey

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]

Initial Performance (IEC Compliant)

Initial luminous flux	25000 lm
-----------------------	----------

Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	145 lm/W
Init. Corr. colour temperature	6500 K
Init. colour rendering index	>80
Initial chromaticity	(0.307, 0.323 SDCM <5
Initial input power	172 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)


Control gear failure rate at median useful life 50000 h	5 %
Median useful life L70B50	70000 h
Lumen maintenance at median useful life* 50000 h	L80

Application Conditions


Ambient temperature range	-30 to +45 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	Not applicable

Product Data

Full product code	871016333666400
Order product name	BY122P G4 LED250S/865 PSU NB
EAN/UPC – product	8710163336664
Order code	33666400
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	911401578551
Net weight (piece)	5.800 kg





Dimensional drawing



CoreLine High-bay BY120P/BY121P

Coreline Highbay Gen4

Photometric data



IFPC1_

IFGU1_

