



# Coreline Highbay Gen4

## BY122P G4 LED250/860 PSD WB

Coreline Highbay Gen4, 183 W, 25500 lm, 6500 K, DALI, 90°, IP65, IK07

CoreLine Highbay Gen4 delivers on the CoreLine promise of innovative, easy-to-use and high-quality luminaires. A reliable, highly efficient luminaire with a very long-lifetime, it delivers great savings on energy and requires less maintenance. At the same time, CoreLine Highbay is very easy to handle. The luminaire can be installed on your existing grid and the electrical connection is a straightforward task, with no need to open the luminaire and an external IP65 connector. With a choice of two beam angles: narrow and wide beam, you can adjust your lighting plan to suit your exact needs. This range also includes Interact Ready luminaires with integrated wireless communications and integrated movement and daylight sensors. So CoreLine Highbay Gen4 is ready to be used with any Interact connected lighting system.

### Product data

General Information		Light Technical	
Light source replaceable	No	Luminous Flux	25,500 lm
Number of gear units	2 units	Correlated Colour Temperature	6500 K
Driver included	Yes	Luminous efficacy (rated) (nom.)	139 lm/W
Light source engine type	LED	Colour rendering index (CRI)	>80
Value ladder	Performance	Beam angle of light source	90 x 90 degree(s)
CE mark	CE mark		
Warranty period	5 years		
Flammability mark	For mounting on easily flammable surfaces		
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 650 °C, duration 30 s
		EU RoHS compliant	Yes

# Coreline Highbay Gen4

Light source colour	865 cool daylight
Optic type	Wide beam
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	90°
Unified Glare Rating (CEN)	26

## Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	60 A
Inrush time	0.6 ms
Power Consumption	183 W
Power Factor (Fraction)	0.95
Connection	Connection unit 3-pole
Cable	Cable 0.3 m with connector 3-pole
Number of products on MCB of 16 A type B	8

## Temperature

Ambient temperature range	-30 to +45 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

## Mechanical and Housing

Housing material	Aluminium
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Aluminium
Housing Colour	Grey
Optical cover/lens finish	Clear
Overall height	464 mm
Overall diameter	510 mm

## Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 0 @200mm to EN62778

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.31, 0.32 SDCM <5
Power consumption tolerance	+/-10%

## Over Time Performance (IEC Compliant)

Driver failure rate at 5,000 hours	0.3 %
Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

## Application Conditions

Performance ambient temperature Tq	35 °C
Maximum dim level	1%
Suitable for random switching	Yes

## Product Data

Order product name	BY122P G4 LED250S/865 PSD WB
Full product name	BY122P G4 LED250/860 PSD WB
Full EOC	871016333882800
Order code	33882800
Material no. (12 NC)	911401582351
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8710163338828
Numerator – packs per outer box	1
EAN/UPC – Case	8710163338828

# Coreline Highbay Gen4

## Dimensional drawing

