



GreenSpace G5

DN390B LED6/830 PSU D100 WH CAU

GreenSpace G5, 5.5 W, 570 lm, 3000 K, High-gloss high reflectance, Matte, Finger-protected

GreenSpace Gen5 is a new LED downlight range combining light efficiency and comfort with product diversity and system compatibility

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
CE mark	CE mark
Warranty period	3 years
Flammability mark	For mounting on normally flammable
	surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Light Technical	
Luminous Flux	570 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	104 lm/W
Color rendering index (CRI)	>80
Beam angle of light source	72 degree(s)
Light source color	830 warm white
Optic type	High-gloss high reflectance
Optical cover type	Transparent bowl with white cover

Luminaire light beam spread	80°	
Operating and Electrical		
Input Voltage	220-240 V	
Line Frequency	50 or 60 Hz	
Inrush current	2.2 A	
Inrush time	0.045 ms	
Power Consumption	5.5 W	
Power Factor (Fraction)	0.9	
Connection	Push-in connector 6-pole	
Cable	Cable with plug	
Number of products on MCB of 16 A type B 48		
Temperature		
Ambient temperature range	-20 to +40 °C	
Controls and Dimming		
Dimmable	No	
Driver/power unit/transformer	Power supply unit (On/Off)	
Control interface	-	


Datasheet, 2023, October 30 data subject to change

GreenSpace G5

Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum die cast
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Black and white
Optical cover finish	Matte
Overall length	0 mm
Overall width	0 mm
Overall height	98 mm
Overall diameter	120 mm
Dimensions (Height x Width x Depth)	98 x 0 x 0 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
ingress protection code	ii zo [i iiigei protecteu]
Mech. impact protection code	IK02 [0.2 J standard]
Mech. impact protection code	IK02 [0.2 J standard]
Mech. impact protection code	IK02 [0.2 J standard]

Initial chromaticity	(0.44,0.403) SDCM<5
Power consumption tolerance	+/-10%
Over Time Performance (IEC Cor	npliant)
Driver failure rate at 5000 h	0.12 %
Median useful life L70B50	50,000 hour(s)
Median useful life L80B50	43,000 hour(s)
Median useful life L90B50	20,000 hour(s)
Application Conditions	
Maximum dim level	Not applicable
Product Data	
Order product name	DN390B LED6/830 PSU D100 WH CAU
Full product name	DN390B LED6/830 PSU D100 WH CAU
Full product code	911401582841
Order code	911401582841
Material Nr. (12NC)	911401582841
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing







© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.