



Mini500 G2

BGP500 LED110/CW PSU A-WB

LED module 12000 lm, Cool white, Power supply unit (On/Off), Tempered glass

In a transparent market like petrol station, operators are under constant pressure to maintain its profitability through lower operating cost, while in the same time attracting more customer with clean and crisp station that gives comfort and safety feeling. Philips' Mini 500 LED is an intuitive undercanopy lighting that ensures optimal visual conditions while enabling huge energy savings. The luminaire's precision-control optics enables light to be distributed where it is needed the most. Its integrated components and long-life LED technology make this an easy-to-install, zero-maintenance solution.

Product data

General Information	
Lamp family code	LED120 [LED module 12000 lm]
Light source replaceable	No
Number of gear units	1 unit
Gear	-
Driver included	Yes
Light source engine type	LED
CE mark	CE mark
Flammability mark	-
ENEC mark	-
Glow-wire test	Temperature 650 °C, duration 30 s
Light Technical	
Luminous Flux	12,000 lm
Correlated Color Temperature (Nom)	6500 K

Luminous Efficacy (rated) (Nom)	120 lm/W
Color rendering index (CRI)	85
Light source color	Cool white
Optic type	Wide beam
Optical cover type	Tempered glass
Luminaire light beam spread	100°
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	100 W
Power Factor (Fraction)	0.95
Connection	-
Number of products on MCB of 16 A type B	11

Mini500 G2

Temperature

Ambient temperature range	-30 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	Yes

Mechanical and Housing

Housing Material	Aluminum die cast
Optic material	Polycarbonate
Optical cover material	Tempered glass
Housing Color	White
Optical cover finish	Clear

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7.5%
Initial chromaticity	-
Power consumption tolerance	+/-10%

Application Conditions

Maximum dim level	Not applicable
-------------------	----------------

Product Data

Order product name	BGP500 LED110/CW PSU A-WB
Full product name	BGP500 LED110/CW PSU A-WB
Full product code	911401583411
Order code	911401583411
Material Nr. (12NC)	911401583411
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

