



# GreenSpace G5

## DN392B LED16/840 PSD D200 ALU CAU

GreenSpace G5, 15.5 W, 1600 lm, 4000 K, DALI, High-gloss high reflectance, Matte, Finger-protected

GreenSpace Gen5 is a new LED downlight range combining light efficiency and comfort with product diversity and system compatibility

### Product data

<b>General Information</b>		<b>Luminaire light beam spread</b>	
Light source replaceable	No	65°	
Number of gear units	1 unit	<b>Operating and Electrical</b>	
Driver included	Yes	Input Voltage	220-240 V
Light source engine type	LED	Line Frequency	50 or 60 Hz
CE mark	CE mark	Inrush current	20.4 A
Warranty period	3 years	Inrush time	0.195 ms
Flammability mark	For mounting on normally flammable surfaces	Power Consumption	15.5 W
Glow-wire test	Temperature 650 °C, duration 30 s	Power Factor (Fraction)	0.95
<b>Light Technical</b>		Cable	Cable with plug
Luminous Flux	1,600 lm	Number of products on MCB of 16 A type B 24	
Correlated Color Temperature (Nom)	4000 K	<b>Temperature</b>	
Luminous Efficacy (rated) (Nom)	110 lm/W	Ambient temperature range	-20 to +40 °C
Color rendering index (CRI)	>80	<b>Controls and Dimming</b>	
Beam angle of light source	60 degree(s)	Dimmable	Yes
Light source color	840 neutral white	Driver/power unit/transformer	Power supply unit with DALI interface
Optic type	High-gloss high reflectance	Control interface	DALI
Optical cover type	Transparent bowl with white cover	Constant light output	No

GreenSpace G5

Mechanical and Housing	
Housing Material	Aluminum die cast
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Black and white
Optical cover finish	Matte
Overall length	0 mm
Overall width	0 mm
Overall height	108 mm
Overall diameter	216 mm
Dimensions (Height x Width x Depth)	108 x 0 x 0 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Initial chromaticity	(0.38,0.38) SDCM<5
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	0.16 %
Median useful life L70B50	50,000 h
Median useful life L80B50	43,000 h
Median useful life L90B50	20,000 h
Product Data	
Order product name	DN392B LED16/840 PSD D200 ALU CAU
Full product name	DN392B LED16/840 PSD D200 ALU CAU
Full product code	911401584941
Order code	911401584941
Material Nr. (12NC)	911401584941
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

