



# GreenSpace G5

## DN392B LED16/830 PSD D150 ALU GM

GreenSpace G5, 15.5 W, 1500 lm, 3000 K, DALI, High-gloss high reflectance, Matte, Finger-protected

GreenSpace Gen5 is a new LED downlight range combining light efficiency and comfort with product diversity and system compatibility

### Product data

General Information		Luminaire light beam spread	
Light source replaceable	No	65°	
Number of gear units	1 unit	Operating and Electrical	
Driver included	Yes	Input Voltage	220-240 V
Light source engine type	LED	Line Frequency	50 or 60 Hz
CE mark	CE mark	Inrush current	20.4 A
Warranty period	3 years	Inrush time	0.195 ms
Flammability mark	For mounting on normally flammable surfaces	Power Consumption	15.5 W
Glow-wire test	Temperature 650 °C, duration 30 s	Power Factor (Fraction)	0.95
Light Technical		Number of products on MCB of 16 A type B 24	
Luminous Flux	1,500 lm	Temperature	
Correlated Color Temperature (Nom)	3000 K	Ambient temperature range	
Luminous Efficacy (rated) (Nom)	97 lm/W	-20 to +40 °C	
Color rendering index (CRI)	>80	Controls and Dimming	
Beam angle of light source	60 degree(s)	Dimmable	Yes
Light source color	830 warm white	Driver/power unit/transformer	Power supply unit with DALI interface
Optic type	High-gloss high reflectance	Control interface	DALI
Optical cover type	Transparent bowl with white cover	Constant light output	No

GreenSpace G5

Mechanical and Housing	
Housing Material	Aluminum die cast
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Black and white
Optical cover finish	Matte
Overall length	0 mm
Overall width	0 mm
Overall height	100 mm
Overall diameter	162 mm
Dimensions (Height x Width x Depth)	100 x 0 x 0 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.44,0.403) SDCM<5

Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	0.16 %
Median useful life L70B50	50,000 hour(s)
Median useful life L80B50	43,000 hour(s)
Median useful life L90B50	20,000 hour(s)
Product Data	
Order product name	DN392B LED16/830 PSD D150 ALU GM
Full product name	DN392B LED16/830 PSD D150 ALU GM
Full product code	872016972020600
Order code	911401585641
Material Nr. (12NC)	911401585641
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169720206
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169720206

Dimensional drawing

