



# SmartPanel 2.0

## RC160V LED34S/865 PSU W60L60

SmartPanel 2.0, 865 cool daylight

SmartPanel 2.0 keeps the design continuity of SmartPanel 1.1 with performance improvement and more cost effective structure. It offers two lumen options with higher system efficacy, 80lm/W @ 4000K. Reliability is improved by the extending of lifetime from 30K hours to 50K hours L70 Ta 25°C

### Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	No
Glow-wire test	Temperature 650 °C, duration 30 s
CE mark	CE mark
ENEC mark	-
Light Technical	
Correlated Color Temperature (Nom)	6500 K
Color rendering index (CRI)	80
Light source color	865 cool daylight
Optic type	Beam angle 60 to 120°
Optical cover type	Transparent bowl with white cover
Luminaire light beam spread	120°
Operating and Electrical	
Input Voltage	220-240 V
Power Consumption	42 W

Power Factor (Fraction)	0.9
Temperature	
Ambient temperature range	-20 to +40 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	Yes
Mechanical and Housing	
Housing Material	Steel
Optic material	Polymethyl methacrylate
Housing Color	White
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

# SmartPanel 2.0

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	RC160V LED34S/865 PSU W60L60
Full product name	RC160V LED34S/865 PSU W60L60

Full product code	911401599811
Order code	911401599811
Material Nr. (12NC)	911401599811
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## Dimensional drawing

