



RoadFlair

BRP394 LED335/NW 280W DM MP1 ILT

RoadFlair, 33500 lm, 280 W, 740 neutral white, Medium beam, Safety class I, Side-entry for diameter 48 to 60 mm

Designed for major and city roads, Philips RoadFlair is a new and exciting product set to brighten your streets beyond imagination. Smartly-designed to bring cities the highest savings possible with best-in-class lumen per watt, this road lighting production comes at a competitive price bound to excite. Philips RoadFlair brings energy efficiency, improves a city's sustainability drive and delivers significant cost reduction in urban environments. The right road luminaire coupled with the right lighting application will create the best environment for your municipality, benefiting local communities and boosting tourism and businesses.

Product data

General Information	
Light source replaceable	No
Driver included	Yes
Light source engine type	LED
CE mark	CE mark
Light Technical	
Luminous Flux	33,500 lm
Standard tilt angle side entry	5°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	119.64 lm/W
Color rendering index (CRI)	>70
Light source color	740 neutral white
Optical cover type	Polycarbonate micro lens optic

Optic type outdoor	Medium beam
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Power Consumption	280 W
Power Factor (Fraction)	0.95
Connection	Mains outlet socket
Cable	Cable 0.5 m without plug
Temperature	
Ambient temperature range	-30 to +50 °C
Controls and Dimming	
Dimmable	No

Constant light output	Programmable
-----------------------	--------------

Mechanical and Housing

Housing Material	Aluminum die cast
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Grey
Mounting device	Side-entry for diameter 48 to 60 mm
Optical cover shape	Ball, globular
Overall length	870 mm
Overall width	295 mm
Overall height	86 mm
Dimensions (Height x Width x Depth)	86 x 295 x 870 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

Protection class IEC	Safety class I
----------------------	----------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-5%
Initial chromaticity	(0.433, 0.401) SDCM>5
Power consumption tolerance	+/-5%

Product Data

Order product name	BRP394 LED335/NW 280W DM MP1 ILT
Full product name	BRP394 LED335/NW 280W DM MP1 ILT
Full product code	911401600204
Order code	911401600204
Material Nr. (12NC)	911401600204
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

